

Floor space:2.9mx2.5m,shipment by container

High efficient chips removal system

Oil-Coolant separating design






■ To separate oil and coolant, the unique design effectively splits the lubrication oil and the coolant. The coolant quality will last long and the machining quality will be guaranteed.

High efficient chips removal mechanism



A simple but efficient removal mechanism can easily convey the chips to the rear side of the machine. The chips cart is convenient for chips disposal.

Full enclosure cover design



Large volume design in coolant tank



- The coolant capacity is above 360 liters. The generated chips heat can be taken away quickly.
- Two coolant tanks are adopted for easy chips removal. They are located under machine to save floor space requirement.

Spindle splash ring



■ Eight splash nozzles on the ring surround the spindle. The splash coolant takes away heat from tool and workpiece to increase the cutting accuracy.

Stable and reliable ATC






- The fast, simple and long-life automatic tool changer provides stable and reliable tool change.
- The innovative cam driven mechanism results in the unique ATC. The bi-directional tool selection is achieved by PLC software programming.
- The ATC reliability has been proved out by over one million running tests.
- The fast ATC saves non-cutting time.
- The cam driven tool magazine ensures rotation accuracy, and smooth motion while full tools loading.

High speed and high accuracy spindle



- The spindle adopts super precision angular contact ball bearings. Spindle speed 6000rpm is standard.
- The four jaws collet provides reliable tool holding force, large contact area, low wear and long service life.
- The high horse power spindle motor is selected for versatile applications. The ZF gearbox is optional for high torque output.
- The advanced high strength timing belt is applied to ensure high torque transmission, no slip and low rotation noise.
- The spindle is dynamically balanced by IRD balancing equipment permitting for field balance calibration. This fully eliminates resonance problems on the spindle while ensuring the best possible machining accuracy.

Spindle oil cooling system



Friendly machine-operator interface





- The control panel meets the safety requirement and rotates easily for operation.
- The automatic diagnosis function displays the malfunction on screen for quick trouble shooting.
- The portable MPG is standard for easing workpiece set-up.
- The pendent arm is designed for easing control panel operation.
- The touch switch, diagram and text on screen make the operation very convenient.

Unique Coolant cooling system for Spindle head and spindle



- The unique coolant cooling system takes away the heat generated at spindle head and spindle. It reduces the spindle head thermal deformation economically.
- ■This outstanding cooling system achieves superior cooling effect without the need of additional pump, filter or hydraulic oil.
- ■The cooling system assures spindle accuracy permanently and extends the service life of the spindle.
- In dry machining conditions, this innovative cooling system provides a circuit to maintain normal cooling performance.





Packing by steel skid and minimizing floor space requirement



- The side mounted control cabinet saves floor space.
- Space by the machine is 2935(W)x2480(D)x2770(H).
- Three machines can be loaded in a 40 feet container to reduce packing and transportation costs.
- The machine is fixed on a steel skid when shipped for convenience and safety.

High speed and high performance cutting



■ Process: Mobile phone mold

■ Workpiece:NAK-80

■ Cutting condition

| - Cutting Condition | | | | | | |
|---------------------|-------|--------------------------|----------------------|-----------------------|----------------|--|
| tool spindle spee | | cutting speed (m/min) | feedrate (mm/min) | cutting depth (mm) | time (min.) | |
| Ø12 end-mill | 6000 | 225 | 2000 | 0.5 | 14 | |
| R2 ball-mill | 10000 | 125 | 4000 | 0.2 | 32 | |
| R3 ball-mill | 10000 | 188 | 2000 | 0.3 | 35 | |
| R3 ball-mill | 10000 | 188 | 4000 | 0.2 | 10 | |
| R1.5 ball-mill | 10000 | 94 | 3000 | 0.1 | 11 | |
| R1 ball-mill | 10000 | 62 | 1000 | 0.1 | 20 | |
| R1 ball-mill | 10000 | 62 | 2000 | 0.05 | 240 | |



■ Process: Glasses mold ■ Workpiece:NAK-80

■ Cutting condition

| tool | | spindle speed (RPM) | cutting speed (m/min) | feedrate (mm/min) | cutting depth (mm) | time (min.) |
|--------|----------|------------------------|--------------------------|----------------------|-----------------------|----------------|
| Ø20 er | nd-mill | 2800 | 176 | 960 | 1 | 65 |
| Ø12 er | nd-mill | 2000 | 75 | 200 | 1 | 26 |
| R6 ba | all-mill | 5000 | 94 | 1200 | 0.6 | 32 |
| R4 ba | all-mill | 6000 | 75 | 750 | 0.6 | 3 |
| R3 ba | all-mill | 8000 | 75 | 1200 | 0.6 | 2 |
| R2 ba | all-mill | 10000 | 62 | 1400 | 0.5 | 230 |



■ Process: Bottle mold ■ Workpiece: NAK-80

■ Workpiece size: 109x109x53 mm

■ Dry cutting

■ Cutting condition

| tool | spindle speed | cutting speed | feedrate | cutting depth | time |
|--------------|---------------|---------------|----------|---------------|--------|
| tooi | (RPM) | (m/min) | (mm/min) | (mm) | (min.) |
| R5 ball-mill | 7000 | 220 | 1000 | 0.5 | 42 |
| R5 ball-mill | 8000 | 251 | 1000 | 0.3 | 23 |
| R4 ball-mill | 8000 | 201 | 1000 | 0.1 | 47 |

MAMIC ISO 238-1

rcularity: +4.5 Pt


Advanced inspection device and technology

The full scale stroke is inspected and ¹⁵compensated by Laser measurement instrument. The motion accuracy can instrument. be ensured.



Spindle dynamic balancing

The IRD dynamic balancing instrument calibrates the spindle displacement, speed, and acceleration of the full speed range.





Ball bar inspection


The Reineshaw ball bar instrument calibrates the circularity and the geometrical accuracy to ensure the precise three dimensional motions.



Machine dimension (mm)







Machine Specification

| MODEL | | CV-1200A | CV-1200B |
|-----------------------------------|--------------|----------------------|----------------------|
| Travel | | | |
| X travel | mm(inch) | 1200 (47.2) | 1200 (47.2) |
| Y travel | mm(inch) | 600 (23.6) | 600 (23.6) |
| Z travel | mm(inch) | 675 (26.6) | 675 (26.6) |
| Spindle nose to table | mm(inch) | 100-775 (3.9-30.5) | 100-775 (3.9-30.5) |
| Spindle | | | |
| Spindle speed | rpm | 8000 | 6000 |
| Automatic tool changer | | | |
| Tool number | no. | 20 | 24 |
| Max tool diameter | mm(inch) | 100(3.9) | 240 (9.4) |
| Max tool length | mm(inch) | 305(12.0) | 305(12.0) |
| Max tool weight | kg(lb) | 7(15.4) | 15(33.1) |
| ATC type | | ARMLESS | ARM |
| Tool shank | | BT/CAT #40 | BT/CAT #50 |
| Motor | | | |
| Spindle motor (cont./30min.rated) | kw(hp) | 11/15 (15/20) | 11/15 (15/20) |
| X/Y/Z servo motor | kw(hp) | 2/2/2 (2.7/2.7/2.7) | 2/2/2 (2.7/2.7/2.7) |
| Table | | | |
| Table size | mm(inch) | 1220×620 (48.0×24.4) | 1220x620 (48.0x24.4) |
| Max load capacity | kg(lb) | 1000(2200) | 1000(2200) |
| T-slot (No. x Width x Distance) | mm(inch) | 5x18x100 (5x0.7x3.9) | 5x18x100 (5x0.7x3.9) |
| Rapid speed | | | |
| X rapid speed | M/min(fpm) | 24 (78.7) | 24 (78.7) |
| Y rapid speed | M/min(fpm) | 24 (78.7) | 24 (78.7) |
| Z rapid speed (Box way) | M/min(fpm) | 18 (59.1) | 18 (59.1) |
| Cutting feedrate | mm/min(ipm) | 1-10000 (0.04-394) | 1-10000 (0.04-394) |
| Controller | | | |
| Mitsubishi | | M64S | M64S |
| Miscellaneous | | | |
| Machine weight | kg(lb) | 8000(17600) | 9000(19800) |
| Power requirement | KVA | 35 | 35 |
| Coolant capacity | L | 360 | 360 |
| Air source | kg/cm² (psi) | 6 (85.3) | 6 (85.3) |

Standard accessories

- Chips auger
- Full enclosure
- Automatic lubrication system
- Spindle coolant cooling
- Base bolt and pad
- Tools box
- Work light
- Alarm light
- M30 automatic power off
- Chips cart

- Portable air gun
- Portable water gun
- Spindle air seal system
- Mechanical, electrical, operation manuals
- Rigid tapping
- Cabinet heat exchanger
- Mechanical oil-coolant separator
- Automatic tool changer
- Telescopic covers

Optional accessories

- Spindle programmable air blow
- Fanuc/Mitsubishi/Siemens controller
- Wash-down system
- Z axis with linenr guide way (#40)
- 10000rpm/12000rpm/14000rpm spindle(#40) X/Y/Z roller guide
- 8000rpm/10000rpm spindle(#50)
- Arm type ATC 24/32 tool stations
- Spindle oil cooling system
- Disc oil-coolant separator
- Coolant through spindle
- Coolant through ballscrew

- Tool probe system
- Touch sensor system
- Deep drill tools holder
- ZF gear box
- Linear scale
- Z axis with brake (without counterweight)
- Spindle splash ring
- 4th axis rotary table

■ The company reserves the rights to modify or to stop adopting the specification of this catalogue.



■ This catalogue is only for reference. The machine may differ to this specification.

Metalwork: 8 Hector Street (West) Osborne Park, Western Australia 6017 Woodwork: 50 Hector Street (West) Osborne Park, Western Australia 6017 Tel: (08) 9445 0700, Fax: (08) 9446 3635 Freecall: 1800 818 448, Email: info@ronmack.com.au

Melbourne Office: Unit 1, 38-40 Little Boundary Road, Laverton North, Victoria 3026

Tel: (03) 9933 7777, Fax: (03) 9314 8988

Agent

ww.ronmack.com.au